

Specification Sheet

Part Number: PC15FT7



Clip is designed for fixation and bundling of tubes and pipes.

Fir Tree Mount Tube Clip, Mounting Hole Dia .25", Panel Thickness .12", PA66HIRHSUV, Black 1000/box

Article Number	151-14303
----------------	-----------

Type	PC15FT7
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Designed to offer a durable single-hole mounting, this tube clip allows the installer to insert the fir tree with minimal force while providing a secure hold.
---------------------	--

Short Description	Fir Tree Mount Tube Clip, Mounting Hole Dia .25", Panel Thickness .12", PA66HIRHSUV, Black 1000/box
-------------------	---

Global Part Name	PC15FT7-PA66HIRHSUV-BK
------------------	------------------------

Length L (Imperial)	0.62
Length L (Metric)	15.75
Fixation Method	Fir Tree
Width W (Imperial)	0.85
Width W (Metric)	21.6
Bundle Diameter Max (Imperial)	0.62
Bundle Diameter Max (Metric)	15.7
Height H (Imperial)	1.5
Height H (Metric)	38.1
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.31
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.25 - 0.27 "
Mounting Hole Diameter D (Metric)	6.4 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.25

Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.8
Disc Diameter (Metric)	21.6
Disc Diameter (Imperial)	0.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)