

Specification Sheet

Part Number: HDM401HIHSUVH4



Mount and tie combination makes it easy to service bundles in the field.

Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.

Eliminates the needs for multiple sized fix diameter clamps.

Medium Torque Cable Tie Mount, Mounting Hole Dia. 0.375", Max Torque 40.0 lb - ft, PA66HIRHSUV, Black, 500/pkg

Article Number	151-07300
----------------	-----------

Type	HDM401
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The arched H-profile of the saddle surface allows for a broad surface contact with the bundle, minimizing pinching and crushing of the bundles, and adjusts to a wide variety of bundle diameters when used with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.
---------------------	---

Short Description	Medium Torque Cable Tie Mount, Mounting Hole Dia. 0.375", Max Torque 40.0 lb - ft, PA66HIRHSUV, Black, 500/pkg
-------------------	--

Global Part Name	HDM401-PA66HIRHSUV-BK
------------------	-----------------------

Length L (Imperial)	1.81
Length L (Metric)	46.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.95
Width W (Metric)	24.0
Height H (Imperial)	0.81
Height H (Metric)	20.7
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.41 "
Mounting Hole Diameter D (Metric)	10.29 mm
Mounting Hole Diameter D Min (Imperial)	0.405
Mounting Hole Diameter D Max (Metric)	10.29
Stud Diameter (Metric)	9.5 mm
Stud Diamater (Imperial)	0.375

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Maximum Torque (kgf-cm)	553
Maximum Torque (lbf-ft)	40
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.