

Specification Sheet

Part Number: 161-63501

Designed for applications that demand high flame retardant materials

Unique open design allows for easy branch-offs at any point along the harness

Overwrap formation provides abrasion protection and accommodates multiple bundle configurations

Flexible construction and design is well suited for applications that involve movement and vibration

Easy-to-use installation tool makes assembly fast and easy



Helawrap, HWPAV030, 1-1/4" (30mm) Dia., PA6V0, Black, 82ft/Reel

Article Number	161-63501
----------------	-----------

Type	HWPAV030
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.
---------------------	---

Short Description	Helawrap, HWPAV030, 1-1/4" (30mm) Dia., PA6V0, Black, 82ft/Reel
Global Part Name	HWPAV030-PA6V0-BK
Contents of pkg/kit	25m + tool
Length L (Imperial)	82.0
Length L (Metric)	25
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	1.14
Bundle Diameter Min (Metric)	29
Bundle Diameter Max (Imperial)	1.26
Bundle Diameter Max (Metric)	32
Diameter D (Imperial)	1.25
Diameter D (Metric)	30.0
Nominal Diameter (Imperial)	1.19
Nominal Diameter (Metric)	30
Wall Thickness WT (Imperial)	0.050
Wall Thickness WT (Metric)	1.30

Material	Polyamide 6 V0 (PA6V0)
Material Shortcut	PA6V0
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EN [45545-2] UL UL 1441
UL Recognized (US)	Yes
Package Quantity (Imperial)	82
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)