

Specification Sheet

Part Number: TAG22J-994



HellermannTyton Inkjet labels are sheet fed for easy loading and fast printing.

Inkjet labels are made with high temperature materials and adhesives so that they will not be affected by the high heat of laser printing.

Inkjet labels are printable using toner for long term UV exposure.

Inkjet labels come in a variety of label sizes and types to fit most applications.

Inkjet Label, Self-Laminating, 1.0" x .5" x 1.63", 32 Per Sheet, PET, White, 1000/pkg

Article Number	593-22994
Type	TAG22J
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton's ink jet self-laminating labels are smear resistant, allowing them to be handled immediately. The labels are made of a heat resistant 1mm polyester film with a strong acrylic based adhesive. The printable area is a special ink-receptive film that absorbs the ink as it is printed on an ink jet printer. Each sheet is smaller than the standard letter size (8.5" x 11".) Less waste results from the smaller sheet size because the user can print smaller quantities at one time. HellermannTyton's ink jet self laminating labels are also more convenient to store.

Short Description	Inkjet Label, Self-Laminating, 1.0" x .5" x 1.63", 32 Per Sheet, PET, White, 1000/pkg
Global Part Name	TAG22J-994-WH
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	0.15
Bundle Diameter Min (Metric)	3.80
Bundle Diameter Max (Imperial)	0.29
Bundle Diameter Max (Metric)	7.37
Thickness T (Metric)	35.0
Width of Liner (Metric)	215.00
Width of Liner (Imperial)	8.5
Outside Diameter Max (Imperial)	0.315
Outside Diameter Min (Metric)	3.8
Outside Diameter Min (Imperial)	0.15
Outside Diameter Max (Metric)	8.00

Material	Type 994, Polyethylene Terephthalate (994)
Material Shortcut	994
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919905060
Labels per Column	4
Labels per Row	8

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)