

Specification Sheet

Part Number: 596-00671

Made with UV-stable inks and materials for durability and weather resistance.

Reflective properties to meet applicable NEC code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.



Solar Label, Reflective, DO NOT DISCONNECT UNDER LOAD, 6.5 x 1.0", VL, Red, 10/pkg

Article Number	596-00671
Type	DNDCUL10
Color	Red (RD)
Quantity Per	pack

Product Description	HellermannTyton makes it easier than ever for solar installers to meet PV labeling codes. Solar Label Convenience Packs allow installers to quickly and economically purchase high quality preprinted NEC code-compliant solar installation labels. Packaged in 10-count quantities to meet the needs of smaller scale solar installations and independent contractors, Solar Label Convenience Packs are available in HellermannTyton's most popular preprinted NEC code-compliant solar label formats. Each Solar Label Convenience Pack contains 10 solar installation labels. Choose from a variety of regular and reflective preprinted labels. For enhanced durability, clear laminate overlay labels are also available in a convenience pack.
Short Description	Solar Label, Reflective, DO NOT DISCONNECT UNDER LOAD, 6.5 x 1.0", VL, Red, 10/pkg
Global Part Name	DNDCUL10-505/281-RD
Local Order Number 2	Cross Reference = 50 per roll: 596-00244
Width W (Imperial)	6.5
Width W (Metric)	165.1
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Type 505/281, UV stabilized, reflective vinyl with clear polyester laminate (505/281)

Material Shortcut	505/281
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014 NEC2011 NEC2020 NEC2017 UL 969
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3919905060
Labels per Column	1

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)