


Specification Sheet

Part Number: 596-96257



Paint Mask Labels provide permanent paint protection but can still be removed at any time when required.

Paint Mask Labels withstand chemicals and heat to survive the painting process.

Paint Mask Label, 2.0" X 1.5" X 4.375", 1 Across, Vinyl, White, 500/RL

Article Number	596-96257
----------------	-----------

Type	PW2.75W2
------	----------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton thermal transfer self-laminating Paint Mask Labels are conformable with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels utilize an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.
---------------------	--

Short Description	Paint Mask Label, 2.0" X 1.5" X 4.375", 1 Across, Vinyl, White, 500/RL
-------------------	--

Global Part Name	PW2.75W2-V-WH
------------------	---------------

Width W (Imperial)	2.0
--------------------	-----

Width W (Metric)	50.8
------------------	------

Bundle Diameter Min (Imperial)	0.62
--------------------------------	------

Bundle Diameter Min (Metric)	15.8
------------------------------	------

Bundle Diameter Max (Imperial)	0.87
--------------------------------	------

Bundle Diameter Max (Metric)	22.2
------------------------------	------

Thickness T (Metric)	64.0
----------------------	------

Height H (Imperial)	1.5
---------------------	-----

Height H (Metric)	38.1
-------------------	------

Width of Liner (Metric)	106.6
-------------------------	-------

Width of Liner (Imperial)	4.2
---------------------------	-----

Material	Vinyl (V)
----------	-----------

Material Shortcut	V
-------------------	---

Adhesive	Acrylic
----------	---------

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Recognized (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com