

Specification Sheet

Part Number: TSRI-JB3



Rubber based foam tape adhesive with high ultimate bond strength conforms to any surface.

Single Gang Junction Box, 2.77" Deep, PVC, Ivory, 1/bg

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 250-00193                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Type                | TSR-JB3                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Color               | Ivory (IV)                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Product Description | Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. all junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base. |
| Short Description   | Single Gang Junction Box, 2.77" Deep, PVC, Ivory, 1/bg                                                                                                                                                                                                                                                                                                                                                                                                   |

|                  |                 |
|------------------|-----------------|
| Global Part Name | TSR-JB3-PVC-BGE |
|------------------|-----------------|

|                     |      |
|---------------------|------|
| Length L (Imperial) | 4.95 |
|---------------------|------|

|                   |        |
|-------------------|--------|
| Length L (Metric) | 125.73 |
|-------------------|--------|

|                    |     |
|--------------------|-----|
| Width W (Imperial) | 3.2 |
|--------------------|-----|

|                  |       |
|------------------|-------|
| Width W (Metric) | 81.28 |
|------------------|-------|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 2.77 |
|---------------------|------|

|                   |       |
|-------------------|-------|
| Height H (Metric) | 70.36 |
|-------------------|-------|

|          |                         |
|----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
|----------|-------------------------|

|                   |     |
|-------------------|-----|
| Material Shortcut | PVC |
|-------------------|-----|

|              |           |
|--------------|-----------|
| Flammability | UL 94 V-0 |
|--------------|-----------|

|              |    |
|--------------|----|
| Halogen Free | No |
|--------------|----|

|                       |    |
|-----------------------|----|
| UV Resistant (Yes/No) | No |
|-----------------------|----|

|                |                     |
|----------------|---------------------|
| Use Conditions | For Indoor Use Only |
|----------------|---------------------|

|                       |                |
|-----------------------|----------------|
| Operating Temperature | +122°F (+50°C) |
|-----------------------|----------------|

|                              |    |
|------------------------------|----|
| Reach Compliant (Article 33) | No |
|------------------------------|----|

|                             |            |
|-----------------------------|------------|
| ROHS Compliant              | Yes        |
| Package Quantity (Imperial) | 1          |
| Package Quantity (Metric)   | 1          |
| Customs Number              | 3925900000 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)