

Specification Sheet

Part Number: 544-21000

Built in storage tray for safe storage of all printing components.

Functions with TagPrint® Pro labeling software for easy label design.

Tested to over 1.5 million strikes without maintenance for reliable embossing.

Fast embossing speed for high volume marker production.



M-BOSS Compact Stainless Steel Embosser with Organizer, Blue, 1/Box

Article Number	544-21000
----------------	-----------

Type	M-BOSS Compact Organiser
------	--------------------------

Color	Blue (BU) White (WH)
-------	----------------------

Quantity Per	pack
--------------	------

Product Description	M-BOSS Compact is a quiet, easy-to-use metal plate embossing printer with a small production footprint. It is simple to install and operate, requiring just a standard electrical supply and a PC. Marker plates are attached to pipes and cables using 4.6mm width MBT cable ties and a MK9SST hand tool.
---------------------	--

Short Description	M-BOSS Compact Stainless Steel Embosser with Organizer, Blue, 1/Box
-------------------	---

Global Part Name	M-BOSS Compact Organiser-MET-BU/WH
------------------	------------------------------------

Length L (Imperial)	19.0
---------------------	------

Length L (Metric)	558
-------------------	-----

Variant	with Organiser
---------	----------------

Width W (Imperial)	18.89
--------------------	-------

Width W (Metric)	480
------------------	-----

Cycle Time	1 second per character
------------	------------------------

Height H (Imperial)	13.89
---------------------	-------

Height H (Metric)	355
-------------------	-----

Depth D (Imperial)	22.44
--------------------	-------

Depth D (Metric)	570
------------------	-----

Diameter D (Imperial)	14.56
-----------------------	-------

Diameter D (Metric)	370
---------------------	-----

Cable Tie Width Max (Imperial)	0.18
--------------------------------	------

Cable Tie Width Max (Metric)	4.6
------------------------------	-----

Power Supply	AC 110V-240V, 45/65 Hz, 1.5A-3A
--------------	---------------------------------

Material	Metal (MET)
Material Shortcut	MET
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	DEKRA EN ISO 12100:2010 CE 2006/42/EG DEKRA EN 60204-1:2006
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8463900080

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)