

Specification Sheet

Part Number: RO514

Compact to easily fit in pants or shirt pockets

Dispenser can be reloaded over and over, making it cost effective to use

Dispenser edge allows easy removal of label liner

Dispenser protects labels from dirt and moisture before use, extending the life and quality of the labels



Rite-On Self-Laminating Label Dispenser, 0.75 x 0.38 x 1.25", VL, White, 200/roll

Article Number 590-05140

Type RO514

Color White (WH) Clear (CL)

Quantity Per pack

Product Description

HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease.

Short Description

Rite-On Self-Laminating Label Dispenser, 0.75 x 0.38 x 1.25", VL, White, 200/roll

Global Part Name	RO514-100B-CL/WH
------------------	------------------

Fixation Method	Pasting / Stick
-----------------	-----------------

Variant	Roller form
---------	-------------

Width W (Imperial)	0.75
--------------------	------

Width W (Metric)	19.05
------------------	-------

Bundle Diameter Min (Imperial)	0.15
--------------------------------	------

Bundle Diameter Min (Metric)	3.89
------------------------------	------

Bundle Diameter Max (Imperial)	0.26
--------------------------------	------

Bundle Diameter Max (Metric)	6.68
------------------------------	------

Height H (Imperial)	0.375
---------------------	-------

Height H (Metric)	9.5
-------------------	-----

Outside Diameter Max (Imperial)	0.263
---------------------------------	-------

Outside Diameter Min (Metric)	3.89
-------------------------------	------

Outside Diameter Min (Imperial)	0.153
---------------------------------	-------

Outside Diameter Max (Metric)	6.68
-------------------------------	------

Material	Type 100B, Vinyl, white transparent, self-laminating (100B)
Material Shortcut	100B
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3919102055

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)