

## Specification Sheet

Part Number: TAG22T2-100B

HellermannTyton Self-Laminating Labels come on rolls on a standard 3" core for easy loading into a printer or caddy.

Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time.

Labels are UL recognized for indoor and outdoor use to expand application options.



HellermannTyton thermal transfer labels work in any thermal transfer printer so that the use always has options to get labels printed without being locked into a single vendor.

Thermal Transfer Adhesive Labels, Self-Laminating, 1.0 x 0.5 x 1.43", 2 Across, VL, White, 5000/roll

|                |           |
|----------------|-----------|
| Article Number | 596-00006 |
|----------------|-----------|

|      |         |
|------|---------|
| Type | TAG22T2 |
|------|---------|

|       |            |
|-------|------------|
| Color | White (WH) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                            |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton thermal transfer self-laminating labels are a conformable vinyl film with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels are UL recognized for indoor and outdoor use with an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires. |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                |                                                                                                      |
|--------------------------------|------------------------------------------------------------------------------------------------------|
| Short Description              | Thermal Transfer Adhesive Labels, Self-Laminating, 1.0 x 0.5 x 1.43", 2 Across, VL, White, 5000/roll |
| Global Part Name               | TAG22T2-100B-WH                                                                                      |
| Width W (Imperial)             | 1.0                                                                                                  |
| Width W (Metric)               | 25.4                                                                                                 |
| Bundle Diameter Min (Imperial) | 0.12                                                                                                 |
| Bundle Diameter Min (Metric)   | 3.04                                                                                                 |
| Bundle Diameter Max (Imperial) | 0.25                                                                                                 |
| Bundle Diameter Max (Metric)   | 6.35                                                                                                 |
| Thickness T (Metric)           | 75                                                                                                   |
| Height H (Imperial)            | 0.5                                                                                                  |
| Height H (Metric)              | 12.7                                                                                                 |
| Width of Liner (Metric)        | 57.1                                                                                                 |
| Width of Liner (Imperial)      | 2.25                                                                                                 |
| Material                       | Type 100B (100B)                                                                                     |

|                                |                                  |
|--------------------------------|----------------------------------|
| Material Shortcut              | 100B                             |
| Adhesive                       | Acrylic                          |
| Halogen Free                   | Yes                              |
| UV Resistant (Yes/No)          | Yes                              |
| Use Conditions                 | For Indoor and Outdoor Use       |
| Adhesive Operating Temperature | -51°F to +200°F (-46°C to +93°C) |
| Operating Temperature          | -40°F to +205°F (-40°C to +96°C) |
| Reach Compliant (Article 33)   | Yes                              |
| ROHS Compliant                 | Yes                              |
| Certification/Specification    | UL-Recognized                    |
| UL Recognized (US)             | Yes                              |
| Package Quantity (Imperial)    | 5007                             |
| Package Quantity (Metric)      | 5000                             |
| Customs Number                 | 3919102055                       |
| Labels per Column              | 1                                |
| Labels per Row                 | 2                                |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)