

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples



Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Features

- Cellular Frequency: 698-960/1710-2690/3300-5925 MHz
- GNSS Frequency Range: 1565-1612 MHz
- Cellular / GNSS Peak Gain: 5.7 / 0.9 dBi
- Cellular / GNSS Efficiency: 73 / 30 %
- Ground Plane Independent
- Flexible to Fit Inside Plastic Enclosures
- Fully Customizable Cable Length and Connector Options

Applications

- Internet of Things (IoT) Devices
- LTE-M, Cat M, Cat M1, NB-IoT
- LTE CAT 1 up to CAT 20 Supported
- CBRS and 5G bands Supported
- Smart Home Networking
- Networking & Telecommunication

Product Image



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

GNSS Frequency Bands Covered

	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	
GPS	■	□	□	
GLONASS	■	□	□	
Galileo	■	□	□	□
BeiDou	□	□	□	
QZSS	■	□	□	□
IRNSS/NAVIC			□	
SBAS	■		□	



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples



Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Electrical Specification

Parameter	Specification					Unit
Operating Frequency	698-960	1565-1612	1710-2690	3300-5000	5150-5925	MHz
Band	5,8,12,13,14,17,18,19,20,26,27,28,29	GNSS (L1/G1)	1,2,3,4,7,9,23,25,30,35,38,39,40	22,42,48,77,78,79	LTE5200/Wi-Fi5800	-
VSWR	3.2	1.5	2.5	2.5	3.3	:1
Peak Gain	2.6	0.9	4.6	5.7	3.7	dBi
Maximum Efficiency	73	30	70	71	56	%
Average Efficiency	56	28.5	60	56	41	%
Impedance	50					Ω
Polarization	Linear					-
Radiation Pattern (Azimuth)	Omni-directional					-
Maximum Input Power	5					W

Mechanical Specification

Parameter	Specification
Antenna Dimensions	119 x 19 x 0.2 mm
Antenna Type	Flexible PCB
Mounting Type	Adhesive Mount
RF Connector ⁽¹⁾	u.FL/IPEX-1/MHF1
RF Cable Type ⁽¹⁾	Ø1.13 mm
Cable Length ⁽¹⁾	94 mm

(1): Fully customizable RF Cable & Connector

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
RoHS Compliance	Yes



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples



Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Ordering Information

Part Number	Description	Connector Option
AANI-FB-0179-1	5G/4G + GNSS Combo Flexible PCB Antenna with IPEX-1 connector & 94 mm cable length	u.FL/IPEX-1/MHF1
AANI-FB-0179-2	5G/4G + GNSS Combo Flexible PCB Antenna with IPEX-4 connector & 94 mm cable length	w.FL/IPEX-4/MHF4
AANI-FB-0179-3	5G/4G + GNSS Combo Flexible PCB Antenna with IPEX-1 connector & 150 mm cable length	u.FL/IPEX-1/MHF1
AANI-FB-0179-4	5G/4G + GNSS Combo Flexible PCB Antenna with IPEX-4 connector & 150 mm cable length	w.FL/IPEX-4/MHF4
AANI-FB-0179-5	5G/4G + GNSS Combo Flexible PCB Antenna with IPEX-1 connector & 200 mm cable length	u.FL/IPEX-1/MHF1
AANI-FB-0179-6	5G/4G + GNSS Combo Flexible PCB Antenna with IPEX-4 connector & 200 mm cable length	w.FL/IPEX-4/MHF4

Note: Different cable and connector configurations that are not listed may be available upon request via [Abracon online support](#)



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Product Dimensions




TOP VIEW



CONNECTOR




u.FL/IPEX-1/MHF1



w.FL/IPEX-4/MHF4



FRONT VIEW



BOTTOM VIEW

PART NUMBER	CABLE LENGTH (L)	CONNECTOR
AANI-FB-0179-1	94	u.FL/IPEX-1/MHF1
AANI-FB-0179-2	94	w.FL/IPEX-4/MHF4
AANI-FB-0179-3	150	u.FL/IPEX-1/MHF1
AANI-FB-0179-4	150	w.FL/IPEX-4/MHF4
AANI-FB-0179-5	200	u.FL/IPEX-1/MHF1
AANI-FB-0179-6	200	w.FL/IPEX-4/MHF4

Unit: mm

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Measurement Setup photo



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples





Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Reflection Characteristics – GNSS Return Loss & VSWR



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples





Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Reflection Characteristics – LTE Return Loss & VSWR



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – GNSS Peak Gain



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – GNSS Total Efficiency (%)



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – LTE Peak Gain



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – LTE Total Efficiency (%)



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – 3D & 2D pattern


3D & 2D Pattern @ 1575 MHz




XY plane



XZ plane



YZ plane



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


3D & 2D Pattern @ 698 MHz




XY plane



XZ plane



YZ plane



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


3D & 2D Pattern @ 960 MHz




XY plane



XZ plane



YZ plane



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples





Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


3D & 2D Pattern @ 1710 MHz




XY plane



XZ plane



YZ plane



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples




Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


3D & 2D Pattern @ 2690 MHz




XY plane



XZ plane



YZ plane



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples







Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 3300 MHz



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples







Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 3800 MHz



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples







Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 5150 MHz



5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples





Check Inventory




119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


3D & 2D Pattern @ 5925 MHz




XY plane



XZ plane



YZ plane



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

5G/4G + GNSS Combo Flexible PCB Antenna



AANI-FB-0179

Request Samples



Check Inventory



119 x 19 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Packaging

1. Number of Antenna/ bags: 50 pcs
2. Total Pcs / package: 500 pcs

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED