

# PanelSeT CRN plain door w/o mount.plate. H200xW200xD150 IP66 IK10 RAL7035..

NSYCRN22150

## Main

Range	PanelSeT	
Product name	PanelSeT CRN	
Application	Multi-purpose	
Category	Compact enclosure	
Enclosure nominal height	200 mm	
Enclosure nominal width	200 mm	
Enclosure nominal depth	150 mm	
Installation accessory type	Wall-mounting	
Device composition	1 body 1 door 1 lock 2 cable gland plate: top and bottom	
Door type	Plain	
Mounting plate description	Without mounting plate	

## Complementary

body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area	
Number of doors	Front face: 1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	3 mm double-bar lock	
Type of gland plate	Standard	
Accessibility for operation	Front	
Removable parts	Door by hinges Cable gland plate by screws	
Material	Body: steel	
Surface finish	Epoxy-polyester powder	
Colour	Grey (RAL 7035)	
Standards	IEC 62208 UL CUL	
Product certifications	UL cUL DNV-GL	
Product weight	2.52 kg	

## **Environment**

IP degree of protection	IP66 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	

## **Packing Units**

r adming dime	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.500 cm
Package 1 Width	21.500 cm
Package 1 Length	21.500 cm
Package 1 Weight	2.520 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	224
Package 2 Height	190.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	577.400 kg

## **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	24
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

#### **Use Again**

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

## **Technical Illustration**

## **Dimensions**



Offer Marketing Illustration

#### **Product benefits / Features**

