


Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples



Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


Features

- Frequency Range: 698-960/1710-2690/3300-5925 MHz
- Peak Gain: 2.4 / 3.6 / 4.8 dBi
- Efficiency: 68% / 68% / 64%
- Ground Plane Independent
- Flexible to Fit Inside Plastic Enclosures
- Fully Customizable Cable Length and Connector Options

Applications

- Internet of Things (IoT) Devices
- CBRS and 5G Bands Supported
- LTE-M, Cat M, Cat M1, NB-IoT
- LTE CAT 1 up to CAT 20 Supported
- Smart Home Networking
- Networking & Telecommunication

Product Image




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples



Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Electrical Specification

Parameter	Specification				Unit
Operating Frequency	698-960	1710-2690	3300-5000	5150-5925	MHz
Band	5,8,12,13,14,17,18,19,20,26,27,28,29	1,2,3,4,7,9,23,25,30,35,38,39,40	22,42,48,77,78,79	LTE5200/Wi-Fi5800	:1
VSWR	3.2	2.0	2.2	3.4	-
Peak Gain	2.4	3.6	4.8	2.1	dBi
Maximum Efficiency	68	68	64	50	%
Average Efficiency	58	59	56	36	
Impedance	50				Ω
Polarization	Linear				-
Radiation Pattern (Azimuth)	Omni-directional				-
Maximum Input Power	5				W

Mechanical Specification

Parameter	Specification
Antenna Dimensions	115.8 x 30.4 x 0.2 mm
Antenna Type	Flexible PCB
Mounting Type	Adhesive Mount
RF Connector ⁽¹⁾	u.FL/IPEX-1/MHF1
RF Cable Type ⁽¹⁾	Ø1.13 mm
Cable Length ⁽¹⁾	100 mm

(1): Fully customizable RF Cable & Connector

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
RoHS Compliance	Yes




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples



Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Ordering Information

Part Number	Description	Connector Option
AANI-FB-0175-1	Wideband 5G/4G Cellular Flexible PCB Antenna with IPEX-1 connector & 100 mm cable length	u.FL/IPEX-1/MHF1
AANI-FB-0175-2	Wideband 5G/4G Cellular Flexible PCB Antenna with IPEX-4 connector & 100 mm cable length	w.FL/IPEX-4/MHF4
AANI-FB-0175-3	Wideband 5G/4G Cellular Flexible PCB Antenna with IPEX-1 connector & 150 mm cable length	u.FL/IPEX-1/MHF1
AANI-FB-0175-4	Wideband 5G/4G Cellular Flexible PCB Antenna with IPEX-4 connector & 150 mm cable length	w.FL/IPEX-4/MHF4
AANI-FB-0175-5	Wideband 5G/4G Cellular Flexible PCB Antenna with IPEX-1 connector & 200 mm cable length	u.FL/IPEX-1/MHF1
AANI-FB-0175-6	Wideband 5G/4G Cellular Flexible PCB Antenna with IPEX-4 connector & 200 mm cable length	w.FL/IPEX-4/MHF4

Note: Different cable and connector configurations that are not listed may be available upon request via [Abracon online support](#)



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A


Product Dimensions




TOP VIEW




FRONT VIEW




BOTTOM VIEW



CONNECTOR



u.FL/IPEX-1/MHF1



w.FL/IPEX-4/MHF4

PART NUMBER	CABLE LENGTH (L)	CONNECTOR
AANI-FB-0175-1	100	u.FL/IPEX-1/MHF1
AANI-FB-0175-2	100	w.FL/IPEX-4/MHF4
AANI-FB-0175-3	150	u.FL/IPEX-1/MHF1
AANI-FB-0175-4	150	w.FL/IPEX-4/MHF4
AANI-FB-0175-5	200	u.FL/IPEX-1/MHF1
AANI-FB-0175-6	200	w.FL/IPEX-4/MHF4

Unit: mm




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Measurement Setup photo



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples





Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Reflection Characteristics – Return Loss & VSWR




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – Peak Gain




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – Total Efficiency (%)




5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED

Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Radiation Characteristics – 3D & 2D pattern

3D & 2D Pattern @ 617 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 698 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 960 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 1710 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 2690 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 3300 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 3800 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 5000 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples




Check Inventory




115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

3D & 2D Pattern @ 5925 MHz



Wideband 5G/4G Cellular Flexible PCB Antenna



AANI-FB-0175

Request Samples



Check Inventory



115.8 x 30.4 x 0.2 mm
RoHS/RoHS II Compliant
MSL Level = N/A

Packaging

1. Number of Antenna/ bags: 50 pcs
2. Total Pcs / package: 500 pcs

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ('COTS'), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-26-25

ABRACON IS
ISO9001-2015
CERTIFIED