

Product data sheet

Specifications



Die cast empty control station,
Harmony XAP, zinc alloy, grey, 2 cut
outs, 22mm, 80x80x51.5mm

XAPG19702

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range of Product	Harmony XAP
Product or Component Type	Die-cast empty control station
Device short name	XAPG
Product destination	For Ø 22 mm control and signalling units
Number of cut-out	2 cut-outs
Colour of base of enclosure	Grey RAL 7032)
Colour of cover	Grey RAL 7032)
Control station type	Metal
Material	Die cast zinc
Sale per indivisible quantity	1
IP degree of protection	IP65 IEC 60529 IP657 IEC 60529
Resistance to chemical agents	Special treatment can be obtained on request

Complementary

Number of vertical rows	2
Number of horizontal rows	1
Cut-out dimensions	Ø 22 mm
Cable entry	cable gland 1 x cable gland
Thread type	3/4 NPT
CAD overall width	3.1 in (80 mm)
CAD overall height	3.1 in (80 mm)
CAD overall depth	2.03 in (51.5 mm)
Product Weight	1.138 lb(US) (0.516 kg)
Compatibility code	XAPG

Environment

Protective treatment	TH
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

IK degree of protection	IK07 IEC 62262
-------------------------	----------------

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
GTIN	3389118381889
Returnability	Yes
Country of origin	MA

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.27 in (8.3 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	3.66 in (9.3 cm)
Package weight(Lbs)	18.2 oz (516.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	14.890 lb(US) (6.754 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	4
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Offer Marketing Illustration

Product benefits / Features

Features XAP



Empty stations for customer assembly with 1 to 10 holes depending on the model



Metal offer for use in a wide range of environments



Operating simplicity, flexibility, and robustness



Full compatibility with Harmony XB4 or Harmony XB5 pushbutton ranges



Pre-drilled or undrilled zinc or aluminium alloy enclosures



Offer Marketing Illustration

Product benefits / Features




Image of product / Alternate images

Alternative



