

Head for push button, Harmony XAC, plastic, white, booted, operating travel 16mm, 25...+ 70 degree C

XACB9211

Main

Range of product	Harmony XAC	
Product or component type	Head for push-button	
Component name	XACB	
Marking	Unmarked	
Operator additional information	Booted	
operating travel	16 mm	
Cap/operator or lens colour	White	
Product compatibility	XESD1191 XESD1291 XESD1181 XESD1281	
Sale per indivisible quantity	10	

Complementary

Product weight 0.005 kg

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4070 °C	
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock resistance	100 gn conforming to IEC 60068-2-27	
Electrical shock protection class	Class II conforming to IEC 61140	
IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK08 conforming to IEC 62262	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.300 cm
Package 1 Width	2.600 cm
Package 1 Length	2.600 cm

Package 1 Weight	6.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.000 cm
Package 2 Width	9.000 cm
Package 2 Length	14.000 cm
Package 2 Weight	69.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	150
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.242 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Total lifecycle Carbon footprint	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Image of product / Alternate images

Alternative









