

Product data sheet

Specifications



ABS industrial box, PanelSeT TBS,
121x105x192mm, int.
105x100x175mm, high plain cover,
IP66, IK07, RAL 7035

NSYTBS191210H

Main

Range	PanelSeT
Device application	Multi-purpose
Category	Industrial box
Height	192 mm
Width	121 mm
Depth	105 mm
Internal height	175 mm
Internal width	105 mm
Internal depth	100 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	High plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	ABS with 45% of post-industrial recycled content
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	650 °C conforming to IEC 60695-2-11
Ambient air temperature for storage	-15...40 °C
Operating temperature	-25...60 °C
Product weight	0.43 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.500 cm
Package 1 Width	12.100 cm
Package 1 Length	19.200 cm
Package 1 Weight	419.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	12.000 cm
Package 2 Width	20.000 cm
Package 2 Length	25.200 cm
Package 2 Weight	839.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	22
Package 3 Height	40.000 cm
Package 3 Width	40.500 cm
Package 3 Length	60.500 cm
Package 3 Weight	10.380 kg

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	3
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Average percentage of recycled plastic content	45 %
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

