# Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



# APC NetShelter Metered Rack PDU, 1U, 15A, 100/120V, 8 NEMA 5-15 outlet

AP7800B

### Overview

Lead time Usually in Stock

# Main

mann		
Product or component type	PDU	
PDU type	Metered	
Cord length	3.7 m	
Number of cables	1	
Provided equipment	Cord retention bracket(s) Installation guide Rack mounting brackets User manual	

# Complementary

Input Voltage	100 V 120 V
Height	4.4 cm
Width	44.4 cm
Output Voltage	120 V
Depth	10.2 cm
Product weight	1.73 kg
Mounting location	Front Rear
Mounting preference	No preference
Input Plug Type	NEMA 5-15P
Mounting mode	Rack-mounted
Rack units	1U
Mounting position	Horizontal
[In] rated current	12 A
Input current limits	15 A
Load capacity	1440 VA
Network frequency	50/60 Hz
Outlet type and quantity	8 NEMA 5-15R

# **Environment**

Product certifications	cUL listed CSA METI Denan UL listed VCCI
Standards	FCC part 15 class A ICES-003 UL 60950
Ambient air temperature for operation	-545 °C
Relative humidity	595 %
Operating altitude	010000 ft
Ambient air temperature for storage	-2565 °C
Storage Relative Humidity	595 %
Storage altitude	015240 m

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	33.7 cm
Package 1 Length	47 cm
Package 1 Weight	2.91 kg

# **Contractual warranty**

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability >

<b>⊘</b> Environmental footprint	
Total lifecycle Carbon footprint	3302
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
Energy Efficiency Optimized	Energy efficient product

### **Use Again**

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Removable battery	Yes
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

# Product data sheet

# **AP7800B**

Image of product / Alternate images

**Alternative** 





