

Socket, SE Relays general purpose relay accessory, 3PDT, 16A, 300 V, 11 pins, screw clamping terminal, 784 series

70-783D11-1A

Product availability: Stock - Normally stocked in distribution facility

Main

Product Range	Legacy	
Product Type	Socket	
Product Compatibility	relay 783XCX suppressor module 70-ASMM diode 70-ASMD signalling device 70-ASMLG suppressor module 70-ASMR	
Number of Terminals	11	
Switch Function	3PDT	
Contact Composition	3 NO + 3 NC	

Complementary

Rated Current	16 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	screw clamp terminals solid for output screw clamp terminals stranded for output
Fixing Mode	By screw M3.5, M3.5 panel Clip-on 35 mm symmetrical rail
Shape of Screw Head	Combination roundhead
Product Weight	1.9 oz (55 g)
Width	1.6 in (40 mm)
Depth	2.2 in (57 mm)

Environment

Ambient Air Temperature for Storage	-40221 °F (-40105 °C)
Ambient Air Temperature for Operation	-40131 °F (-4055 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL
	CSA
	CE

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480278174
Returnability	Yes
Country of origin	TW

Packing Units

r doming office	
Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.31 in (8.4 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	1.18 in (3.0 cm)
Package weight(Lbs)	1.9 oz (55.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	3.35 in (8.5 cm)
Package 2 Width	2.45 in (6.22 cm)
Package 2 Length	8.00 in (20.32 cm)
Package 2 Weight	24.7 oz (700.5 g)
Unit Type of Package 3	BB1
Number of Units in Package 3	100
Package 3 Height	8.58 in (21.8 cm)
Package 3 Width	12.87 in (32.7 cm)
Package 3 Length	17.28 in (43.9 cm)
Package 3 Weight	35.3 lb(US) (16.0 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	1	

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Dimensions Drawings

Approximate Dimensions

