

Selector switch head, Harmony 9001K, metal, standard handle, black, 30mm, 3 positions, spring return right to center

9001KS73B

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product or Component Type | Head for selector switch | |
|---------------------------|--|--|
| Device short name | К | |
| Enclosure type | Dust and oil resistant weatherproof enclosure indoor/outdoor | |
| Mounting diameter | 1.2 in (30 mm) | |
| Range of Product | Harmony 9001K | |

Complementary

| • | | |
|-------------------------------|-------------------------------|--|
| Bezel material | Metal | |
| Cap/operator or lens colour | black | |
| Contacts type and composition | Without contact block | |
| Operator position information | 3 positions | |
| Operator profile | Standard handle | |
| Operator profile | 1 projecting push-button | |
| Size | 30 mm | |
| Type of operator | Spring return right to centre | |
| Cap/operator or lens colour | Black | |
| Type of operator | Spring return | |
| Contacts type and composition | Without contact block | |

Environment

| NEMA Degree of Protection | NEMA 1/2/3/3R/4/6/12/13 | |
|---------------------------|---|--|
| Product Certifications | UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 | |
| | CE | |

Ordering and shipping details

| Category | US10CS121426 | |
|-------------------|--------------|--|
| Discount Schedule | 0CS1 | |
| GTIN | 785901820758 | |
| Returnability | No | |
| Country of origin | MX | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------|--------------------|--|
| Nbr. of units in pkg. | 1 | |
| Package 1 Height | 2.00 in (5.08 cm) | |
| Package 1 Width | 2.30 in (5.842 cm) | |
| Package 1 Length | 2.80 in (7.112 cm) | |
| Package weight(Lbs) | 4.32 oz (122.47 g) | |

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

| Materials and Substances | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| SCIP Number | Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d |
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again

| ○ Repack and remanufacture | | |
|----------------------------|--|--|
| Take-back | No | |
| WEEE Label | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | |

Technical Illustration

Dimensions

