

PENDANT STATION 600VAC 10AMP XAC SPECIAL

XACA0432891405

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range of Product	Harmony XAC	
Product or Component Type	Pendant control station	
Device short name	XACA	

Complementary

Control station type	Double insulated	
Enclosure Material	Polypropylene	
Electrical circuit type	Control circuit	
Enclosure Type	Complete ready for use	
Control station composition	4 push-buttons	
Connections - terminals	Screw clamp terminals, 1 x 2.5 mm 2 with or without cable end Screw clamp terminals, 2 x 1.5 mm 2 with or without cable end	
Protective treatment	тн	
Ambient air temperature for operation	-13158 °F (-2570 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Overvoltage category	Class II conforming to IEC 61140	
IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK08 conforming to EN 50102	
Mechanical durability	1000000 cycles	

Ordering and shipping details

Category	US10CS222473	
Discount Schedule	0CS2	
GTIN	3606487519539	
Returnability	Yes	

Packing Units

Unit Type of Package 1	PCE	
Nbr. of units in pkg.	1	
Package 1 Height	13.97 in (35.484 cm)	
Package 1 Width	5.50 in (13.97 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	35.48 in (90.129 cm)
Package weight(Lbs)	32.799 oz (929.864 g)

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No