

Product data sheet

Specifications

SQUARE D



NEMA combination starter, Type S, 60A fusible disconnect, Size 2, 45A, 10HP at 240VAC, 3 phase, 3 pole, Motor Logic SSOLR, 120VAC coil, NEMA 12 [TAA]

8538SDASP4

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	45 A
Number of Poles	3P
Horsepower Rating	10 hp 200 V AC, 3 phase 10 hp 230 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Auxiliary Contacts	2 NO + 2 NC
Thermal overload type	Solid state Motor Logic class 10/20 15...45 A
Disconnect Type	Fusible disconnect switch H and K, 60 A, electrical SPDT
NEMA size	2
Height	27.75 in (704.85 mm)
Depth	9.59 in (243.59 mm)
Width	10.5 in (266.7 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10CP121213
Discount Schedule	0CP1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	785901876427
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	12.40 in (31.5 cm)
Package 1 Width	14.02 in (35.6 cm)
Package 1 Length	32.09 in (81.5 cm)
Package weight(Lbs)	50.99 lb(US) (23.13 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Not compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
-----------	----