

Wall mounted polyester enclosure, PanelSeT PLM, plain door, 647x436x250mm, IP66, IK10, RAL 7035

NSYPLM64G

Main

Range	PanelSeT	
Device short name	PLM	
Enclosure type	Multi-purpose	
Category	Compact enclosure	
Nominal height	647 mm	
Nominal width	436 mm	
Nominal depth	250 mm	
Enclosure mounting	Wall mounted	
Device composition	1 body 1 door 2 lock	
Door type	Plain	
Lock type	3 mm double-bar lock	

Complementary

Number of locks	2	
Mounting plate description	Without mounting plate	
Accessibility for operation	Front	
Removable parts	Door by hinges	
Material	Polyester reinforced with fibreglass	
Colour	Grey (RAL 7035)	
Standards	NEMA classification 13 NEMA classification 4X IEC 62208	
Product certifications	UL	
Electrical insulation class	Class II	

Environment

IP degree of protection	IP66 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	
Fire resistance	960 °C conforming to IEC 62208	
Ambient air temperature for operation	-4080 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	28.500 cm
Package 1 Width	46.000 cm
Package 1 Length	71.500 cm
Package 1 Weight	9.750 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	21
Package 2 Height	204.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	220.000 kg

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	76
Environmental Disclosure	Product Environmental Profile

Use Better

Average percentage of recycled plastic content	37 %
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	B279f58f-9c73-4621-a0a0-f9f4e0aa66d8
REACh Regulation	REACh Declaration
PVC free	Yes

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Image of product / Alternate images

Alternative











Image of product in real life situation

