

# GUPXCB150CD150

## GUTOR PXC UL Battery Cabinet, 150A Breaker, 150 Watt/Cell Battery



### Overview

|              |                                                                                                                                       |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | Fully populated, VRLA battery cabinets. Includes all breakers and fuses, line up and match capability, top and/or bottom cable entry. |
| Lead time    | Usually Ships within 3 Weeks                                                                                                          |

### Main

|              |      |
|--------------|------|
| Battery Type | VRLA |
|--------------|------|

### Physical

|               |                            |
|---------------|----------------------------|
| Height        | 82.72 in (210.1 cm)        |
| Width         | 30.31 in (77 cm)           |
| Depth         | 31.50 in (80 cm)           |
| Net Weight    | 1500.00 lb(US) (680.39 kg) |
| Mounting Mode | Not rack-mountable         |

### Conformance

|           |                                |
|-----------|--------------------------------|
| Standards | FCC Part 15 class A<br>UL 1778 |
|-----------|--------------------------------|

### Environmental

|                                       |                                 |
|---------------------------------------|---------------------------------|
| Ambient Air Temperature for Operation | 14...104 °F (-10...40 °C)       |
| Operating altitude                    | 0...9842 ft                     |
| Relative Humidity                     | 0...95 % non-condensing         |
| Ambient Air Temperature for Storage   | 5...104 °F (-15...40 °C)        |
| Storage altitude                      | 0...16404 ft (0.00...4999.94 m) |
| Storage Relative Humidity             | 0...95 % Non-condensing         |

### Batteries & Runtime

|                                |                          |
|--------------------------------|--------------------------|
| Battery Placement              | Battery Cabinet          |
| Battery Slots Empty            | 0                        |
| Included Battery Modules       | 0                        |
| Battery manufacturer           | C&D and EnerSys          |
| Device mounting                | Enclosed battery cabinet |
| Battery Volt-Amp-Hour Capacity | 0 VAh                    |

### Ordering and shipping details

|                       |                             |
|-----------------------|-----------------------------|
| Nbr. of units in pkg. | 1                           |
| Package weight(Lbs)   | 1596.65 lb(US) (724.228 kg) |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type of Package 1       | PCE                 |
| Package 1 Height             | 90.71 in (230.4 cm) |
| Package 1 width              | 54.02 in (137.2 cm) |
| Package 1 Length             | 38.50 in (97.8 cm)  |
| Number of Units in Package 3 | 1                   |

### Contractual warranty

|          |                     |
|----------|---------------------|
| Warranty | 1 year (parts only) |
|----------|---------------------|