

Product data sheet

Characteristics

9001K3L35LR

illuminated pushbutton Ø 30 - spring return
metallic guard - 24/28 V AC/DC

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

| | |
|---------------------------------|----------------------------------|
| Range of product | Harmony 9001K |
| Product or component type | Complete illuminated push-button |
| Device short name | 9001K |
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.18 in (30 mm) |
| Operator additional information | Extended metallic guard |
| Light source | LED red |

Complementary

| | |
|------------------------------|------------------------|
| Shape of signaling unit head | Round |
| Type of operator | Spring return |
| Operator profile | Flush unmarked |
| Bulb base | BA 9s |
| Light block supply | Direct |
| Mechanical durability | 5000000 cycles |
| Operating position | Any position |
| Product weight | 0.37 lb(US) (0.166 kg) |

Environment

| | |
|---------------------------------------|--|
| Standards | EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14 |
| Product certifications | NEMA UL 508 |
| Protective treatment | TC |
| Ambient air temperature for storage | -40...158 °F (-40...70 °C) |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C) |
| Vibration resistance | 7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 |
| Electrical shock protection class | Class II conforming to IEC 61140 |
| IP degree of protection | IP66 conforming to IEC 60529 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.5 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| - - - - - Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to www.p65warnings.ca.gov |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|