

Product data sheet

Specifications



Harmony, pendant station,
emergency stop operator, push to
maintain, turn to release, 30 mm
mushroom, red

ZA2BS834

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XAC
Product or Component Type	Head for emergency switching off push-button
Sale per indivisible quantity	1

Complementary

Product Compatibility	XACA..
Mounting Location	Front of enclosure
Overvoltage category	Class II conforming to IEC 61140
Operator profile	Red mushroom Ø 30 mm
Product Weight	0.09 lb(US) (0.04 kg)
Marking	Unmarked

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
IK degree of protection	IK08
Standards	CSA C22.2 No 14 IEC 60947-5-1 UL 508 IEC 60204-32 IEC 60947-5-5 IEC 62262
Vibration resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
GTIN	3389110591750
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nbr. of units in pkg.	1
Package 1 Height	1.38 in (3.500 cm)
Package 1 Width	2.76 in (7.000 cm)
Package 1 Length	3.15 in (8.000 cm)
Package weight(Lbs)	1.481 oz (42.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	40
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	3.968 lb(US) (1.800 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative



