

Wall mounted enclosure, PanelSeT S3X, stainless steel 304L, plain door, 300x200x150mm, IP66

NSYS3X3215

Main

Range	Spacial	
Product name	Spacial S3X	
enclosure type	Multi-purpose	
category	Compact enclosure	
nominal height	300 mm	
nominal width	200 mm	
nominal depth	150 mm	
product installation	Wall-mounting	
Device composition	1 body	
	1 lock: door	
	1 door	

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail	
Door type	Plain	
Number of doors	Front face: 1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	3 mm double-bar lock	
Mounting plate description	Without mounting plate	
Type of gland plate	Without gland plate	
Accessibility for operation	Front	
Removable parts	Door by hinges	
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel	
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated	
Product weight	3.08 kg	

Environment

Standards	IEC 62208 UL CUL
Product certifications	UL 508 type A CAN/CSA 22

IP degree of protection	IP66 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	
Environmental characteristic	Corrosive Specific hygiene	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.500 cm
Package 1 Width	21.000 cm
Package 1 Length	31.500 cm
Package 1 Weight	2.930 kg
Unit Type of Package 2	P12
Number of Units in Package 2	168
Package 2 Height	180.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	507.200 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Total lifecycle Carbon footprint	44
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

