

Product data sheet

Specifications

SQUARE D



Foot Switch, Harmony, industrial, unshielded, two stage, 5A at 600 VAC, SPDT contact each stage, NEMA 2, 4, 13 enclosure

9002AW5

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	9002AW
Product	Foot switch
Contact Operation	2 steps
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPDT per step
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Unshielded
Operator Action	Spring return
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508
Height	3.9 in (99 mm)
Width	4.5 in (114 mm)
Depth	8.5 in (216 mm)

Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
GTIN	785901816003
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	4.80 in (12.192 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	9.00 in (22.86 cm)
Package weight(Lbs)	3.230 lb(US) (1.465 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)

11

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile

No need of specific recycling operations

Take-back

No

WEEE Label

 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative



