

PanelSeT CRN plain door with mount.plate. H400xW300xD200 IP66 IK10 RAL7035..

NSYCRN43200P

Main

Range	PanelSeT
Product name	PanelSeT CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	400 mm
Enclosure nominal width	300 mm
Enclosure nominal depth	200 mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door with lock 1 mounting plate
Door type	Plain
Mounting plate description	Plain

Complementary

•		
body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area	
Number of doors	Front face: 1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	3 mm double-bar lock	
Type of gland plate	Standard	
Accessibility for operation	Front	
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element	
Material	Enclosure: steel Mounting plate: galvanised steel	
Surface finish	Enclosure: epoxy-polyester powder	
Colour	Enclosure: grey (RAL 7035)	
Standards	IEC 62208 UL CUL	
Product certifications	cUL UL DNV-GL	
Product weight	6.946 kg	

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

r adming dime	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.500 cm
Package 1 Width	31.000 cm
Package 1 Length	42.000 cm
Package 1 Weight	6.946 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	64
Package 2 Height	180.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	456.500 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	65
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142	
REACh Regulation	REACh Declaration	

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

