

Socket, General Purpose Relays, for 782 relays, 3PDT, 11 pins, output lift terminals solid/stranded, separate contact, 25A, 300V

70-788EL11-1

Product availability: Stock - Normally stocked in distribution facility

Main

Product Range	Legacy	
Product Type	Socket	
Product Compatibility	relay 788XBXR/XCXR suppressor module 70-ASMM diode 70-ASMD signalling device 70-ASMLG	
Number of Terminals	11	
Switch Function	3PDT	
Contact Composition	3 NO + 3 NC	

Complementary

Rated Current	25 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Separate
Connections Terminals	lift terminals solid for output lift terminals stranded for output
Tightening Torque	< 0.8 N.m
Fixing Mode	Clip-on 35 mm symmetrical DIN rail
Product Weight	3.4 oz (96 g)
Width	1.4 in (36 mm)
Depth	2.2 in (57 mm)

Environment

Ambient Air Temperature for Storage	-40221 °F (-40105 °C)
Ambient Air Temperature for Operation	-40131 °F (-4055 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL
	CSA
	CF

Ordering and shipping details

Category US10CP221127

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2
GTIN	3606480278198
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.78 in (9.6 cm)
Package 1 Width	1.42 in (3.6 cm)
Package 1 Length	2.48 in (6.3 cm)
Package weight(Lbs)	3.4 oz (96 g)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	1	

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Dimensions Drawings

Approximate Dimensions




Image of product / Alternate images

Alternative

