

# Product data sheet

Specifications



PanelSeT CRN tspt door w/o  
mount.plate. H300xW250xD150  
IP66 IK10 RAL7035..

NSYCRN325150T

**Product availability:** Non-Stock - Not normally stocked in distribution facility

## Main

Range	PanelSeT
Product name	PanelSeT CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	11.8 in (300 mm)
Enclosure nominal width	9.8 in (250 mm)
Enclosure nominal depth	5.9 in (150 mm)
Installation accessory type	Wall-mounting
Device composition	1 body 1 cable gland plate 1 door 1 lock
Door type	Glass
Mounting plate description	Without mounting plate

## Complementary

body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	Body steel Door steel and security glass
Surface finish	epoxy-polyester powder
color	Gray RAL 7035)
Standards	IEC 62208 UL CUL
Product Certifications	cUL UL DNV-GL
Product Weight	8.219 lb(US) (3.728 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK08 IEC 62262

## Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
GTIN	3606480212598
Returnability	No
Country of origin	ES

## Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	6.69 in (17.000 cm)
Package 1 Width	10.24 in (26.000 cm)
Package 1 Length	12.60 in (32.000 cm)
Package weight(Lbs)	8.219 lb(US) (3.728 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	147
Package 2 Height	80.71 in (205.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	1241.204 lb(US) (563.000 kg)

## Contractual warranty

Coverage	Core product
Warranty	18 months



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	35
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better

#### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACH Regulation	<a href="#">REACH Declaration</a>

### Use Again

#### Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions

---



## Offer Marketing Illustration

### Product benefits / Features

---




Image of product / Alternate images

Alternative

---

