

Product data sheet

Specifications



Illuminated push-button head,
Harmony 9001K, metal, projecting,
green, 30mm, spring return, LED
green, 24-28V

9001K2L35LGG

Main

Range of product	Harmony 9001K
Product or component type	Head for illuminated push-button
Device short name	9001K
Mounting diameter	30 mm
Light source	Green LED

Complementary

Bezel material	Metal
Shape of signaling unit head	Round
Type of operator	spring return
Operator profile	Green projecting, unmarked
Bulb base	BA 9s
Light block supply	Direct 24...28 V AC/DC
Contacts type and composition	Without contact block
Mechanical durability	5000000 cycles
Operating position	Any position
Product weight	0.166 kg
Cap/operator or lens colour	Green
[Us] rated supply voltage	24...28 V
Light source colour	Green
Type of operator	Spring return
Operator profile	Projecting

Environment

Standards	UL 508 IEC 60947-5-4 JIS C 852 JIS C 4520 IEC 60947-1 IEC 60947-5-1 CSA C22.2 No 14
Product certifications	NEMA UL 508
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C

Ambient air temperature for operation	-25...70 °C
Vibration resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.903 cm
Package 1 Width	5.08 cm
Package 1 Length	32.774 cm
Package 1 Weight	226.796 g



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins