

Wall mounted enclosure, PanelSeT S3X, stainless steel 304L, plain door, 600x400x200mm, IP66

NSYS3X6420

Main

Range	Spacial	
Product name	Spacial S3X	
enclosure type	Multi-purpose	
category	Compact enclosure	
nominal height	600 mm	
nominal width	400 mm	
nominal depth	200 mm	
product installation	Wall-mounting	
Device composition	1 body	
	1 door	
	2 lock: door	
	2 perforated vertical profile drilled: door	

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail	
Door type	Plain	
Number of doors	Front face: 1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	2 points lock, 3 mm double-bar	
Mounting plate description	Without mounting plate	
Type of gland plate	Without gland plate	
Accessibility for operation	Front	
Removable parts	Door by hinges	
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel	
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated	
Product weight	9.446 kg	

Environment

Standards	IEC 62208
	UL
	CUL

Product certifications	UL 508 type A CAN/CSA 22	
IP degree of protection	IP66 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	
Environmental characteristic	Specific hygiene Corrosive	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.500 cm
Package 1 Width	41.000 cm
Package 1 Length	61.000 cm
Package 1 Weight	9.446 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	30
Package 2 Height	198.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	307.000 kg

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	140
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

