

Wall mounted enclosure, PanelSeT S3X, stainless steel 304L, plain door, 300x250x150mm, IP66

NSYS3X302515

Product availability: Stock - Normally stocked in distribution

Main

Range	Spacial
Product name	Spacial S3X
enclosure type	Multi-purpose
category	Compact enclosure
nominal height	11.8 in (300 mm)
nominal width	9.8 in (250 mm)
nominal depth	5.9 in (150 mm)
product installation	Wall-mounting
Device composition	1 body
	1 lock door
	1 door

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Solid
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface finish	Body and door Scotch-Brite® brushed Lock chromium plated
Product Weight	7.78 lb(US) (3.53 kg)

Environment

Standards	IEC 62208 UL CUL
Product Certifications	UL 508 type A CAN/CSA 22

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Environmental characteristic	Specific hygiene Corrosive

Ordering and shipping details

	· · · · ·
Category	US10ES180034
Discount Schedule	0ES1
GTIN	3606480155031
Returnability	Yes
Country of origin	BG

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	6.50 in (16.500 cm)
Package 1 Width	10.24 in (26.000 cm)
Package 1 Length	12.60 in (32.000 cm)
Package weight(Lbs)	7.782 lb(US) (3.530 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	147
Package 2 Height	78.74 in (200.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	1170.457 lb(US) (530.910 kg)

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	51
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

