

Wall mounted steel enclosure, PanelSeT S3D, plain door, with mounting plate, 400x400x200mm, IP66, IK10

NSYS3D4420P

### Main

Range	PanelSeT
Product name	PanelSeT S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	400 mm
Enclosure nominal width	400 mm
Enclosure nominal depth	200 mm
Door type	Plain
Mounting plate description	Plain
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	body mounting plate door with lock cable gland plate

## Complementary

body type	Gutter-shaped front rail double sheet thickness Single piece body	
Number of doors	Front face: 1 door(s)	
Door opening side	Reversible (120 °)	
Lock type	3 mm double-bar lock	
Accessibility for operation	Front	
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element	
Material	Enclosure: steel Mounting plate: galvanised steel	
Surface finish	Enclosure: epoxy-polyester powder	
Colour	Enclosure: grey (RAL 7035)	
Standards	IEC 62208 UL CUL	
Product certifications	UL cUL DNV GL BV	

Product weight 8 kg

## **Environment**

NEMA degree of protection	NEMA 4X/13	
IK degree of protection	IK10 conforming to IEC 62262	
IP degree of protection	IP66 conforming to IEC 60529	

# **Packing Units**

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	42.000 cm
Package 1 Width	42.000 cm
Package 1 Length	42.000 cm
Package 1 Weight	8.670 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	40
Package 2 Height	182.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	360.500 kg

# **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	92
Environmental Disclosure	Product Environmental Profile

### **Use Better**


Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No

## **Technical Illustration**

## **Dimensions**



Offer Marketing Illustration

#### **Product benefits / Features**

