

# Product data sheet

## Characteristics

# 9001K43J35FLH1

Illuminated selector switch, Harmony 9001K, metal, long handle, blue, 30mm, 3 positions, stay put, 24-28V, 1 C/O



### Main

Range of Product	Harmony 9001K
Product or Component Type	Illuminated selector switch
Device short name	K
Type of operator	maintained
Operator profile	Gloved hand knob

### Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Operator position information	3 positions
Contacts type and composition	1 C/O
Connections - terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1
Device presentation	Complete product
Cap/operator or lens colour	Blue
[Us] rated supply voltage	24...28 V
Light block supply	Full voltage
Operator profile	Long handle
Type of operator	Stay put
Size	30 mm
Bulb base	BA 9s
Light source	Incandescent bulb
Cam profile	3

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR

### Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901895558
Returnability	No
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	8.80 oz (249.476 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------