

Head for push button, Harmony XAC, plastic, white, booted, operating travel 16mm, 25...+ 70 degree C

XACB9211

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XAC	
Product or Component Type	Head for push-button	
Component name	XACB	
Marking	Unmarked	
Operator additional information	Booted	
operating travel	0.6 in (16 mm)	
Cap/operator or lens colour	White	
Product Compatibility	XESD1191	
	XESD1291	
	XESD1181	
	XESD1281	
Sale per indivisible quantity	10	

Complementary

Net Weight 0.011 lb(US) (0.005 kg)

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1	
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock resistance	100 gn IEC 60068-2-27	
Electrical shock protection class	Class II conforming to IEC 61140	
IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK08 conforming to IEC 62262	

Ordering and shipping details

Category	US10CS222473
Discount Schedule	0CS2
GTIN	3389110640922
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country of origin US

Packing Units

PCE	
1	
0.91 in (2.300 cm)	
1.02 in (2.600 cm)	
1.02 in (2.600 cm)	
0.212 oz (6.000 g)	
BB1	
10	
1.57 in (4.000 cm)	
3.54 in (9.000 cm)	
5.51 in (14.000 cm)	
2.434 oz (69.000 g)	
S01	
150	
5.91 in (15.000 cm)	
5.91 in (15.000 cm)	
15.75 in (40.000 cm)	
2.738 lb(US) (1.242 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Image of product / Alternate images

Alternative









