

Product data sheet

Specifications



Empty handy box, Harmony XB5R, plastic, dark grey, 1 cut out, 22mm

ZBRM01

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XB5R
Product or Component Type	Empty handy box
Device short name	ZBRM
Mounting diameter	0.9 in (22 mm)
Product destination	For XB5R Ø 22 mm control units
Control station application	One function

Complementary

Colour of base of enclosure	Dark grey RAL 7016)
Colour of cover	Dark grey RAL 7016)
Material	Polycarbonate
Product Weight	0.4 lb(US) (0.2 kg)

Environment

Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Standards	ETSI EN 301 489-1 ETSI EN 300 440-1 ETSI EN 300 440-2 ETSI EN 301 489-3 UL 508 CSA C22.2 No 14 IEC 60947-5-1
Product Certifications	C-tick FCC ANATEL RSS BT 2006/95/EC GOST CE SRRC
Directives	2004/108/EC - electromagnetic compatibility 1999/5/EC - R&TTE directive

Ordering and shipping details

Category	US1000I22470
----------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0001
GTIN	3606480334696
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.27 in (8.3 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	3.66 in (9.3 cm)
Package weight(Lbs)	3.5 oz (98.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.849 lb(US) (4.014 kg)

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle)

1

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

SCIP Number

25b7f895-3732-43c8-9910-ef6005058640

California proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture

Circularity Profile

[End of Life Information](#)


Take-back

No

Dimensions Drawings

Wireless and Batteryless Pushbutton - Transmitter

Plastic Handy Box for Mobile Use




(1) Location for ZBY0101T legend.

(2) Location for magnet to be stuck on by the customer.

Mounting and Clearance

Mounting of Empty Mobile Box



- (1): Transmitter
- (2): Fixing nut
- (3): Empty mobile box
- (4): Pushbutton

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative





