

metal conduit box UL, Altivar, Nema type1, IP21, for variable speed drive, size 6

VW3A9704

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Altivar	
Accessory / separate part category	Protection accessory	
Accessory / Separate Part Type	IP21 protection kit	
Product compatibility	Variable speed drive ATV630 55 kW, normal duty 200240 V	
	Variable speed drive ATV630 75 kW, normal duty 200240 V	
	Variable speed drive ATV630 110 kW, normal duty 380480 V	
	Variable speed drive ATV630 132 kW, normal duty 380480 V	
	Variable speed drive ATV630 160 kW, normal duty 380480 V	
	Variable speed drive ATV630 90 kW, heavy duty 380480 V	
	Variable speed drive ATV630 110 kW, heavy duty 380480 V	
	Variable speed drive ATV630 132 kW, heavy duty 380480 V	
	Variable speed drive ATV610 110 kW 380480 V	
	Variable speed drive ATV610 132 kW 380480 V	
	Variable speed drive ATV610 160 kW 380480 V	
	Variable speed drive ATV930 55 kW, normal duty 200240 V	
	Variable speed drive ATV930 75 kW, normal duty 200240 V	
	Variable speed drive ATV930 110 kW, normal duty 380480 V	
	Variable speed drive ATV930 132 kW, normal duty 380480 V	
	Variable speed drive ATV930 160 kW, normal duty 380480 V	
	Variable speed drive ATV930 45 kW, heavy duty 200240 V	
	Variable speed drive ATV930 55 kW, heavy duty 200240 V	
	Variable speed drive ATV930 90 kW, heavy duty 380480 V	
	Variable speed drive ATV930 110 kW, heavy duty 380480 V	
	Variable speed drive ATV930 132 kW, heavy duty 380480 V	
Accessory / separate part destination	Variable speed drive	
Range Compatibility	Easy Altivar 610	
	Altivar Process ATV600	
	Altivar Process ATV900	

Complementary

Kit composition	Instruction sheet Fixing accessories All the mechanical parts including a pre-cut plate for fixing the cable glands
Net Weight	19.8 lb(US) (9 kg)

Ordering and shipping details

Category	US1CP4E22205
Discount Schedule	CP4E
GTIN	3606485410876
Returnability	Yes
Country of origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.40 in (31.500 cm)
Package 1 Width	14.61 in (37.100 cm)
Package 1 Length	15.94 in (40.500 cm)
Package 1 Weight	23.067 lb(US) (10.463 kg)
Unit Type of Package 2	P12
Number of Units in Package 2	18
Package 2 Height	43.31 in (110.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	444.232 lb(US) (201.500 kg)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Efdd96fa-877d-491d-af5a-b4069bcf028e
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes
e Again	

○ Repack and remanufacture		
Take-back	No	