



NEMA Motor Starter, Type S, nonreversing, Size 6, 540A, 400 HP at 460 VAC, up to 100 kA SCCR, 3 phase, 3 pole, Motor Logic, 120 VAC coil, open [TAA]

8536SHO2V02H30S

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

Complementary

NEMA Size	6	
Rated Current	540 A	
Number of Poles	3P	
Maximum Voltage Rating	600 V AC	
Phase	3 phase	
Type of Overload	Solid state Motor Logic class 10/20	
Horsepower Rating	150 HP 200 V AC 200 HP 230 V AC 400 HP 460 V AC 400 HP 575 V AC	
SCCR	Circuit-breaker 800 A maximum: 65 kA at 480 V AC Fuse J 600 A maximum: 100 kA at 600 V AC Fuse T 600 A maximum: 100 kA at 600 V AC Fuse RK1 600 A maximum: 100 kA at 600 V AC Fuse RK5 600 A maximum: 100 kA at 600 V AC	
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Control Circuit Type	Control circuit transformer	
Control Units	No control units	
Pilot Light	Without pilot light	
Auxiliary Contacts	Without	
Other Equipment	2 fuses (primary), 2 fuses (secondary)	
Terminal Type	Screw clamp terminals	
Height	28.06 in (712.72 mm)	
Width	12.34 in (313.44 mm)	
Depth	9.00 in (228.60 mm)	

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Enclosure Type	Not rated (open device)	
Certifications	UL Listed	
	CSA	
	NEMA	

Ordering and shipping details

Category	US10CP121195
Discount Schedule	0CP1
GTIN	785901924609
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	13.50 in (34.29 cm)	
Package 1 Width	12.00 in (30.48 cm)	
Package 1 Length	30.50 in (77.47 cm)	
Package 1 Weight	78.981 lb(US) (35.825 kg)	

Compliance

Compliance TAA

Contractual warranty

Warranty 18 months

Jul 4, 2025



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances		
Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Not compliant	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Use Again

○ Repack and remanufacture	
Take-back	No