

Earth-leakage add-on protection module VigiPacT, ComPacT NSX 100/160, 200VAC to 440VAC, 30mA to 30A, 3 poles

LV429488

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range of Product	ComPacT NSX100250 ComPact NSX100250	
Device short name	VigiPacT	
Product or Component Type	Vigi add-on	
Device Application	Wiring	
Range compatibility	ComPacT ComPacT NSX100 circuit breaker ComPacT ComPacT NSX160 circuit breaker ComPact ComPact NSX100 circuit breaker ComPact ComPact NSX100 circuit breaker	
Poles description	3P	
Line Rated Current	100 A 160 A	
Earth-leakage protection class	Class A Class AC	
Residual earth-leakage sensitity adjustment type	Adjustable	
Earth-leakage sensitivity	0.03 A class A 0.1 A class A 0.3 A class A 0.5 A class A 1 A class A 3 A class A 10 A class AC	
Residual earth-leakage time delay adjustment type	Adjustable	
[∆t] residual earth-leakage time delay adjustment	0 ms 60 ms 150 ms 300 ms 500 ms 800 ms 1.2 s 4 s	

### Complementary

•		
Network type	CA	
Network Frequency	50/60 Hz	
[Ue] rated operational voltage	200440 V AC 50/60 Hz IEC 60947-2	
Earth-leakage protection	With	
Maximum breaking time	800 ms	
Overvoltage category	IV	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

Electrical shock protection class	Class II
Standards	IEC 60947-2

# Ordering and shipping details

Category	US10DE201103
Discount Schedule	0DE2
GTIN	3606481298546
Returnability	No
Country of origin	IT

## **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	5.12 in (13.000 cm)	
Package 1 Width	5.71 in (14.500 cm)	
Package 1 Length	6.69 in (17.000 cm)	
Package 1 Weight	2.410 lb(US) (1.093 kg)	
Unit Type of Package 2	S04	
Number of Units in Package 2	12	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	15.75 in (40.000 cm)	
Package 2 Length	23.62 in (60.000 cm)	
Package 2 Weight	30.281 lb(US) (13.735 kg)	
Unit Type of Package 3	P12	
Number of Units in Package 3	48	
Package 3 Height	16.54 in (42.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	47.24 in (120.000 cm)	
Package 3 Weight	148.151 lb(US) (67.200 kg)	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	28
Environmental Disclosure	Product Environmental Profile

### **Use Better**

Materials and Substances	
Recycled metal content at CR level	0
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	Ef27149b-fb4f-412f-9539-28ab12115a54
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Halogen content performance	Product contains halogen above thresholds

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.