

Protective rear cover, Harmony XAP, for plastron XAPE301, insulated material, without opening, IP 65

XAPE901

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range of Product	Harmony XAP	
Product or Component Type	Protective rear cover	
Device short name	XAPE	
Product destination	For front plate XAPE301	
Material	Insulated material	
Cable entry	Knock-out cable entries	
Product mounting	Flush mounting	
IP degree of protection	IP65 IEC 60529 IP657 NF C 20-010	
Resistance to chemical agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts	

# Complementary

Net Weight	0.09 lb(US) (0.04 kg)	

## **Environment**

Protective treatment	TC TH
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient Air Temperature for Operation	-13158 °F (-2570 °C)
Electrical shock protection class	Class I conforming to IEC 60536

# Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
GTIN	3389110628104
Returnability	Yes
Country of origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 in (8.000 cm)
Package 1 Width	2.05 in (5.200 cm)
Package 1 Length	2.36 in (6.000 cm)
Package 1 Weight	1.376 oz (39.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	36
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	3.924 lb(US) (1.780 kg)

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

<b>⊗</b> Materials and Substances	
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

## **XAPE901**

## **Dimensions Drawings**

## **Dimensions and Mounting**



#### P Usable depth

b		Р	
mm	in.	mm	in.
52	2.05	82.5	3.25