



Foot Switch, Harmony 9002AW, industrial, oversized pedal and safety and side shields, SPDT contact, NEMA 4, 13, two stage, 5A at 600V AC

9002AW117

Product availability: Stock - Normally stocked in distribution facility

Main

Range	9002AW	
Product	Foot switch	
Contact Operation	1 step	
Certifications	UL Listed	
	CSA	
Cable Entry	0.75 inch NPT conduit entrance	
Contact Arrangement	SPDT	
Enclosure Rating	NEMA 2/4/13	
Voltage Rating	600 V AC/DC	
Protection	Oversized pedal shield	
	Safety door	
	Side shield	
Operator Action	Spring return	
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508	
	10 A 240 V AC inductive control circuit UL 508	
	6 A 480 V AC inductive control circuit UL 508	
	5 A 600 V AC inductive control circuit UL 508	
	15 A 120 V AC resistive control circuit UL 508	
	0.5 A 125 V DC resistive control circuit UL 508	
Height	6.3 in (159 mm)	
Width	6.4 in (163 mm)	
Depth	8.5 in (217 mm)	

Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
GTIN	785901652410
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	6.50 in (16.510 cm)	
Package 1 Width	6.80 in (17.272 cm)	
Package 1 Length	11.30 in (28.702 cm)	
Package 1 Weight	11.451 lb(US) (5.194 kg)	
Unit Type of Package 2	PAL	
Number of Units in Package 2	36	
Package 2 Height	40.00 in (101.600 cm)	
Package 2 Width	40.00 in (101.600 cm)	
Package 2 Length	48.00 in (121.920 cm)	
Package 2 Weight	415.999 lb(US) (188.694 kg)	

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	38	

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Image of product / Alternate images

Alternative















