

Empty enclosure control station, Harmony 9001K, Harmony 9001SK, stainless steel, 3 cut outs, 30mm

9001KYSS3

Product availability: Stock - Normally stocked in distribution facility

Main

| Range of Product | Harmony 9001SK Harmony 9001K |
|---------------------------|----------------------------------|
| Product or Component Type | Empty enclosure |
| Device short name | 9001K |
| Number of cut-out | 3 cut-outs |
| Cable entry | 1 entry tapped for 3/4" knockout |

Complementary

| Product destination | For Ø 30 mm control and signalling units | |
|---------------------|--|--|
| Material | Stainless steel | |
| Net Weight | 3.781 lb(US) (1.715 kg) | |

Environment

| Protective treatment | TH |
|---------------------------------------|--|
| Ambient Air Temperature for Storage | -40158 °F (-4070 °C) |
| Ambient Air Temperature for Operation | -13158 °F (-2570 °C) |
| Overvoltage category | II conforming to IEC 61140 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 3 NEMA 4 NEMA 4X |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| GTIN | 785901017509 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|---------------------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 5.00 in (12.700 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Width | 5.20 in (13.200 cm) |
|------------------------------|----------------------------|
| Package 1 Length | 11.50 in (29.210 cm) |
| Package 1 Weight | 3.840 lb(US) (1.742 kg) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 2 |
| Package 2 Height | 5.91 in (15.000 cm) |
| Package 2 Width | 11.81 in (30.000 cm) |
| Package 2 Length | 15.75 in (40.000 cm) |
| Package 2 Weight | 8.058 lb(US) (3.655 kg) |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 32 |
| Package 3 Height | 17.72 in (45.000 cm) |
| Package 3 Width | 31.50 in (80.000 cm) |
| Package 3 Length | 47.24 in (120.000 cm) |
| Package 3 Weight | 155.382 lb(US) (70.480 kg) |

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

| Materials and Substances | |
|--|--|
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again


| ○ Repack and remanufacture | |
|----------------------------|----|
| Take-back | No |

9001KYSS3

Dimensions Drawings

Dimensions

Below drawing shows a 3-hole enclosure. Refer to the product characteristics to get the number of holes



(1) Knockout conduit thread: 3/4".

| а | | G | |
|-----|-------|-----|------|
| mm | in. | mm | in. |
| 260 | 10.24 | 244 | 9.61 |

Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001K



Jul 12, 2025

Image of product / Alternate images

Alternative











