

Socket, General Purpose Relays, for 750H/750 relays, DPDT, 8 pins, screws clamp terminals, 10...15A, 300...600V

70-464-1

Product availability: Stock - Normally stocked in distribution facility

Main

Product Range	Legacy	
Product Type	Socket	
Product Compatibility	relay 750XBXR relay 750XBXH	
Number of Terminals	8	
Switch Function	DPDT	
Contact Composition	2 NO + 2 NC	

Complementary

•		
Rated Current	10 A	
	15 A	
[Ue] rated operational voltage	300600 V	
Contact Terminal Arrangement	Mixed	
Connections Terminals	screw clamp terminals solid for output	
	screw clamp terminals stranded for output	
Tightening Torque	Screw < 1 N.m	
	Screw < 0.8 N.m	
Fixing Mode	By screw M3.5, M3.5 panel	
	Clip-on 35 mm DIN rail	
Shape of Screw Head	Combination roundhead	
Product Weight	1.4 oz (40 g)	
Width	1.6 in (40 mm)	
Depth	2.2 in (57 mm)	

Environment

Ambient Air Temperature for Storage	-40221 °F (-40105 °C)
Ambient Air Temperature for Operation	-40131 °F (-4055 °C)
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

Ordering and shipping details

Category US10CP221127

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2	
GTIN	3606480277962	
Returnability	Yes	
Country of origin	CN	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.02 in (2.6 cm)
Package 1 Width	1.73 in (4.4 cm)
Package 1 Length	2.20 in (5.6 cm)
Package 1 Weight	1.3 oz (36 g)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	1	

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	No

Dimensions Drawings

Approximate Dimensions

