

Product data sheet

Specifications



plug-in solid state relay - 12.5 mm - output - 24 V DC - 2 A

ABS7SC3BA

**Product availability: Non-Stock - Not normally stocked in
distribution facility**

Main

Range of Product	Advantys Telefast ABE7
Product or Component Type	Plug-in solid state relay
Relay Type	Output relay
minimum ordered quantity	Set of 4

Complementary

Response time	<= 0.1 ms from state 1 to 0 <= 0.2 ms from state 0 to 1
Width pitch dimension	0.5 in (12 mm)
Product Compatibility	ABE7P16T318 ABE7P16T330 ABE7R16T330 ABE7P16T334 ABE7P16T318E ABE7P16T330E ABE7R16T332
Discrete input voltage	24 V DC
Discrete output voltage	24 V DC self-protected
Discrete output current	2000 mA
Current state 0 guaranteed	0.4 mA DC
Current state 1 guaranteed	2.9 mA DC
Voltage state 0 guaranteed	3.8 V DC
Voltage state 1 guaranteed	18.6 V DC
Net Weight	0.035 lb(US) (0.016 kg)

Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
GTIN	3389110720761
Returnability	No
Country of origin	LV

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.97 in (5 cm)
Package 1 Width	2.05 in (5.2 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	0.5 oz (13 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	1.97 in (5 cm)
Package 2 Width	2.05 in (5.2 cm)
Package 2 Length	2.56 in (6.5 cm)
Package 2 Weight	1.8 oz (52 g)
Unit Type of Package 3	S02
Number of Units in Package 3	128
Package 3 Height	5.91 in (15 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	4.548 lb(US) (2.063 kg)

Contractual warranty

Warranty	18 months
-----------------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation

[REACH Declaration](#)

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

PVC free

Yes

Use Again

Repack and remanufacture

Circularity Profile

No need of specific recycling operations

Take-back

No

Connections and Schema

Internal Wiring Diagram




Image of product / Alternate images

Alternative

