

Product data sheet

Specifications

SQUARE D



Foot Switch, Harmony 9002AW, industrial, pedal and side shields, SPST contact, maintained contact, NEMA 2, 4, 13, 3A at 230V AC

9002AW12

Product availability: Stock - Normally stocked in distribution facility

Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	UL Listed CSA
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPST
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Pedal shield Side shield
Operator Action	Maintained
Rated Breaking Capacity	6 A 115 V AC inductive control circuit UL 508 3 A 230 V AC inductive control circuit UL 508 2.2 A 125 V DC inductive control circuit UL 508 2.2 A 125 V DC resistive control circuit UL 508 1.1 A 250 V DC inductive control circuit UL 508 1.1 A 250 V DC resistive control circuit UL 508
Height	4.8 in (123 mm)
Width	5.4 in (137 mm)
Depth	9.02 in (229 mm)

Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
GTIN	785901817406
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.71 in (14.5 cm)
Package 1 Width	5.91 in (15.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	11.89 in (30.2 cm)
Package 1 Weight	4.48 lb(US) (2.03 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	15

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Image of product / Alternate images

Alternative



