

Socket, SE Relays general purpose relay accessory, DPDT, 15A, 300 V, 8 pins, screw clamp terminal, 750R/750H series

70-169-1

Product availability: Stock - Normally stocked in distribution facility

Main

Product Range	Legacy	
Product Type	Socket	
Product Compatibility	relay 750XBXR relay 750XBXH relay TDRPRO-5101/5102	
Number of Terminals	8	
Switch Function	DPDT	
Contact Composition	2 NO + 2 NC	

Complementary

Rated Current	15 A	
[Ue] rated operational voltage	300 V	
Contact Terminal Arrangement	Mixed	
Connections Terminals	screw clamp terminals, AWG 14AWG 12 Panel screw clamp terminals, clamping connection capacity:2 x 2.52 x 4 mm², AWG 14AWG 12 stranded for output	
Tightening Torque	0.9 N.m	
Fixing Mode	By screw M3.5, M3.5 panel	
Shape of Screw Head	Combination roundhead	
Product Weight	2.01 oz (57 g)	
Width	2.0 in (50 mm)	
Depth	2.2 in (57 mm)	

Environment

Ambient Air Temperature for Storage	-40221 °F (-40105 °C)	
Ambient Air Temperature for Operation	-40131 °F (-4055 °C)	
IP Degree of Protection	IP20	
Flame Retardance	UL94-V0	
Product Certifications	UL	
	CSA	
	CE	

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10CP221127
Discount Schedule	0CP2
GTIN	3606480277771
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.70 in (1.778 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	2.30 in (5.842 cm)
Package 1 Weight	1.440 oz (40.824 g)



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
China RoHS Regulation	China RoHS declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture			
Take-back	No		
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		

Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams

