

heat sink, Easy Harmony Solid State Relays, panel mounting, thermal resistance 0.82 degree C W

SSP1HP08

Product availability: Stock - Normally stocked in distribution facility

Main

| Range of Product | Easy Harmony Solid State Relays |
|---------------------------|---------------------------------|
| Product or Component Type | Heat sink |

Complementary

| Product compatibility | solid state relay SSR 10 A panel solid state relay SSR 25 A panel | |
|-------------------------------|--|--|
| thermal resistance | 0.82°C/W | |
| Mounting Support | Panel | |
| Overvoltage category | III | |
| Pollution degree | 2 | |
| Sale per indivisible quantity | 1 | |
| Width | 2.8 in (72 mm) | |
| Height | 2.4 in (60 mm) | |
| Depth | 2.4 in (60 mm) | |
| Net Weight | 6.3 oz (179.1 g) | |
| Device presentation | Complete product | |

Ordering and shipping details

| Category | US10CP222375 | |
|-------------------|---------------|--|
| Discount Schedule | 0CP2 | |
| GTIN | 3606487050681 | |
| Returnability | Yes | |
| Country of origin | CN | |

Packing Units

| Unit Type of Package 1 | PCE |
|------------------------------|------------------|
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.36 in (6 cm) |
| Package 1 Width | 2.36 in (6 cm) |
| Package 1 Length | 2.36 in (6 cm) |
| Package 1 Weight | 6.3 oz (179.1 g) |
| Unit Type of Package 2 | S02 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Number of Units in Package 2 | 40 | |
|------------------------------|-----------------------|--|
| Package 2 Height | 5.91 in (15 cm) | |
| Package 2 Width | 11.81 in (30 cm) | |
| Package 2 Length | 15.75 in (40 cm) | |
| Package 2 Weight | 19.2 lb(US) (8.7 kg) | |
| Unit Type of Package 3 | P12 | |
| Number of Units in Package 3 | 1920 | |
| Package 3 Height | 41.34 in (105 cm) | |
| Package 3 Width | 31.50 in (80 cm) | |
| Package 3 Length | 47.24 in (120 cm) | |
| Package 3 Weight | 950.2 lb(US) (431 kg) | |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ⊘ Environmental footprint | |
|--|-------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 2 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| Packaging made with recycled cardboard | No |
|--|---|
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Use Again

| ○ Repack and remanufacture | |
|----------------------------|-------------------------|
| Circularity Profile | End of Life Information |
| Take-back | No |

Image of product / Alternate images

Alternative











