

Illuminated push button, Harmony 9001K, metal, mushroom 41mm, red, 30mm, 2 positions, push pull, 24...28V, 1 CO

9001KR9P35RH13

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range of Product	Harmony 9001K	
Product or Component Type	Illuminated push-button	
Device short name	К	
Type of operator	push-pull	
Operator profile	Red mushroom Ø 41 mm	
Operator additional information	Screw-on plastic	

# Complementary

Bezel material	Metal	
Mounting diameter	1.2 in (30 mm)	
Light source	incandescent	
Light source	Incandescent bulb	
Bulb base	BA 9s	
Light block supply	Direct	
[Us] rated supply voltage	2428 V AC/DC	
Contacts type and composition	1 C/O	
Connections - terminals	Screw clamp terminals	
Operating position	Any position	
[le] rated operational current	10 A, AC-15 10 A, DC-13	
Contact operation	Standard	
Device presentation	Complete product	
Cap/operator or lens colour	Red	
[Us] rated supply voltage	2428 V	
Light block supply	Full voltage	
Operator profile	Mushroom Ø 41 mm	
Type of operator	Push-pull	
Operator position information	2 positions	
Size	30 mm	

## **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CSA LR 25490 class 3211 03 CE UL listed file E42259 CCN NKCR NEMA
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
GTIN	785901034278
Returnability	Yes
Country of origin	MX

# **Packing Units**

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	1.97 in (5.000 cm)	
Package 1 Width	2.17 in (5.500 cm)	
Package 1 Length	4.53 in (11.500 cm)	
Package 1 Weight	6.490 oz (184.000 g)	
Unit Type of Package 2	P06	
Number of Units in Package 2	384	
Package 2 Height	29.53 in (75.000 cm)	
Package 2 Width	31.50 in (80.000 cm)	
Package 2 Length	23.62 in (60.000 cm)	
Package 2 Weight	183.777 lb(US) (83.360 kg)	

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### **Use Again**

○ Repack and remanufacture		
Take-back	No	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	

Offer Marketing Illustration

#### **Product benefits / Features**



## 9001KR9P35RH13

Offer Marketing Illustration

#### Product benefits / Features

# **Technical Benefits**

## Harmony 9001K

