



Overview

Presentation	APC Basic Rack PDUs distribute reliable rack power distribution via a single input with multiple output receptacles. Easily mount this vertical PDU in racks or enclosures. It occupies zero U of valuable rack space, which allows space for more equipment in the rack. This vertical PDU does not require additional tools to mount into APC NetShelter Enclosures. Enables a quick recovery from overload events. Packaging Includes PDU, Installation guide, Rack Mounting brackets, Toolless Mounting Kit.
Lead time	Usually in Stock

Main

Main Input Voltage	100 V 120 V
Main Output Voltage	100 V 120 V
Plug standard	NEMA 5-15P
Number of rack unit	0U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Toolless Mounting Kit

Physical

Color	Black
Height	24.02 in (61 cm)
Width	1.73 in (4.4 cm)
Depth	1.73 in (4.4 cm)
Net Weight	4.81 lb(US) (2.18 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	12 A
Acceptable Input Voltage	100...125 V
Input current limits	15 A
Load Capacity	1400 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	14 NEMA 5-15R
--------------------------------	---------------

Conformance

Product Certifications	CUL Listed METI Denan UL Listed
------------------------	---------------------------------------

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304207061
Package weight(Lbs)	6.44 lb(US) (2.92 kg)

Packing Units

Package 1 Height	25.51 in (64.8 cm)
Package 1 width	7.01 in (17.8 cm)
Package 1 Length	5.98 in (15.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------